



CT50175C0UG, Cable Tie, 50 Lb Tensile, Black, Universal Grade

By Burndy
Catalog # [CT50175C0UG](#)



Universal Grade Cable Tie, 8 IN L, 0.18 IN W, Color: Black, Material: Nylon 6/6 UV, Tensile Strength: 50 LB.

Features

Standard Cable Tie

Application

For General Purpose

General

Color	UV Black
EU RoHS Indicator	Yes
Material	NYLON 6/6
Rating - Minimum Tensile Strength lbs	50
Sub Brand	UNIRAP,CABLE TIE
Tool Type	Standard
Trade Name	UNIRAP™
Type	UG, Standard
UPC	781810469125

Dimensions

Dimension - Bundle Diameter Max inch	1.75
Dimension - L Length Overall mm	199 mm
Dimension - Length Overall inch	7.83 in
Dimension - Width inch	0.18 in
Dimension - Width mm	4.6 mm

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	Yes
Certification - UV Rated	Yes
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	9000
Minimum Pack Quantity	100

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Product Cross Section Image\(s\) - BUR_CT_UNIRAP_CABLE_TIE_LineArt](#)
[Sales Drawings - 10092186](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-CT50175C0UG-SPEC-EN | REV 5/2024