



## CT50175C3, Cable Tie, 1.75" Max Bundle, 50 Lb Tensile, Orange

By Burndy  
Catalog # [CT50175C3](#)



Nylon cable ties, Tensile strength-50 Lbs, Color- Orange, 07.56"L, 0.18"W, 01.87" Bundle Dia.

### Features

Standard Cable Tie

### General

Catalog Number	CT50175C3
Color	Orange
Material	NYLON 6/6
Operating Temperature Celcius Max	85 °C
Operating Temperature Celcius Min	-40 °C
Rating - Minimum Tensile Strength lbs	50
Tool Type	Standard
Trade Name	UNIRAP™
UPC	781810332474

### Dimensions

Dimension - Bundle Diameter Max inch	1.875
Dimension - L Length Overall mm	192 mm
Dimension - Length Overall inch	7.56 in
Dimension - Width inch	0.18 in
Dimension - Width mm	5 mm

### Certifications And Compliance

Certification - 94V0 Rated	No
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - UV Rated	No
Certification - cULus	No
Military Spec Number	MS3367-1-3
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Carton Quantity	1000
Minimum Pack Quantity	100
Packaging Type	Bag

### Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section G - Wire Management](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_CT\\_UNIRAP\\_CABLE\\_TIE\\_LineArt](#)
- [Sales Drawings - 50080813](#)
- [Specifications - CT50175C3](#)