




CT50175IDC, Cable Tie, 1.81" Max Bundle, 50 Lb Tensile, Natural, Identification

By Burndy
Catalog # [CT50175IDC](#)



Nylon cable ties, Tensile strength-50 Lbs, Color- Natural, 07.91"L, 0.18"W, 01.81" Bundle Dia.

Features

Identification

General

Catalog Number	CT50175IDC
Color	Natural
Material	NYLON 6/6
Military Specification	MS3368
Operating Temperature Celcius Max	85 °C
Operating Temperature Celcius Min	-40 °C
Rating - Minimum Tensile Strength lbs	50
Trade Name	UNIRAP™
UPC	781810335383

Dimensions

Dimension - Bundle Diameter Max inch	1.81 in
Dimension - L Length Overall mm	201 mm
Dimension - Length Overall inch	7.91 in
Dimension - Marking Pad Size inch	1 X 7/16
Dimension - Width inch	0.18 in

Dimension - Width mm 5 mm

Certifications And Compliance

Certification - 94V0 Rated	N
Certification - CSA Approved	No
Certification - UV Rated	No
Industry Standard(s)	Military Specified (Mil-Spec)
Military Spec Number	MS3368-1-A
Standards - Industry Standards Met	Military Specified (Mil-Spec)
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	1000
Minimum Pack Quantity	1000
Packaging Type	Bag

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section G - Wire Management](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_CT_ID_UNIRAP_CABLE_TIE_LineArt](#)
- [Sales Drawings - 50080813](#)
- [Specifications - CT50175IDC](#)