

# CT50175M, Cable Tie, 1.75" Max Bundle, 50 Lb Tensile, Natural

By Burndy  
Catalog # CT50175M



Natural Nylon 6/6 Cable Tie, 1.75" Max. Bundle Dia, 50 Lbs, 8" Long, 0.18" Wide.

## Features

- Standard Cable Tie
- Suitable for General Use
- Most sizes are available in Natural or Black

## Application

For General Purpose

## General

Catalog Number	CT50175M
Color	Natural
EU RoHS Indicator	Yes
Material	NYLON 6/6
Military Specification	MS3367
Operating Temperature Celcius Max	85 °C
Operating Temperature Celcius Min	-40 °C
Rating - Minimum Tensile Strength lbs	50
Sub Brand	UNIRAP,CABLE TIE
Trade Name	UNIRAP™
Type	Standard
UPC	781810332559

## Dimensions

Dimension - Bundle Diameter Max inch	1.875
Dimension - L Length Overall mm	192 mm
Dimension - Length Overall inch	7.56 in

Dimension - Width inch	0.18 in
Dimension - Width mm	5 mm

## Certifications And Compliance

Buy American Compliant	Yes
Certification - 94V0 Rated	N
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - UV Rated	No
Certification - cULus	No
Industry Standard(s)	Military Specified (Mil-Spec)
Military Spec Number	MS3367-1-9
Standards - Industry Standards Met	Military Specified (Mil-Spec)
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Carton Quantity	10000
Minimum Pack Quantity	1000

## Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section G - Wire Management](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_CT\\_UNIRAP\\_CABLE\\_TIE\\_LineArt](#)
- [Sales Drawings - 50080813](#)
- [Specifications - CT50175M](#)