



# CT50175M0UG, Cable Tie, 1.75" Max Bundle, 50 Lb Tensile, UV Black, Universal Grade



By Burndy  
Catalog # [CT50175M0UG](#)

Nylon cable ties, Tensile strength-50 Lbs, Color- UV Black, 07.83"L, 0.18"W, 01.75" Bundle Dia.

## Features

Standard Cable Tie

## General

|                |              |
|----------------|--------------|
| Catalog Number | CT50175M0UG  |
| Color          | Black        |
| Material       | NYLON 6/6    |
| Tool Type      | Standard     |
| Trade Name     | UNIRAP™      |
| UPC            | 781810469132 |

## Dimensions

|                                      |         |
|--------------------------------------|---------|
| Dimension - Bundle Diameter Max inch | 1.75    |
| Dimension - L Length Overall mm      | 199 mm  |
| Dimension - Length Overall inch      | 7.83 in |
| Dimension - Width inch               | 0.18 in |
| Dimension - Width mm                 | 4.6 mm  |

## Certifications And Compliance

|                                    |     |
|------------------------------------|-----|
| Certification - CSA Approved       | No  |
| Certification - ETL                | No  |
| Certification - UL Recognized      | Yes |
| Certification - UV Rated           | Yes |
| Certification - cULus              | No  |
| Standards - RoHS Compliance Status | CM  |
| UL Listed                          | No  |

## Logistics

|                       |       |
|-----------------------|-------|
| Carton Quantity       | 11000 |
| Minimum Pack Quantity | 1000  |

## Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section G - Wire Management](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_CT\\_UNIRAP\\_CABLE\\_TIE\\_LineArt](#)
- [Sales Drawings - 10092186](#)
- [Specifications - CT50175M0UG](#)