



CT50175MH10C0, Cable Tie, 1.75" Max Bundle, 50 Lb Tensile, UV Black, Screw Mount

By Burndy
Catalog # [CT50175MH10C0](#)

UV Black Nylon 6/6 Mounting Hole Cable Tie, # 10 Stud, 1.75"
Max. Bundle Dia, 50 Lbs, 8.50" Long, 0.18" Wide.



Features

Mounting Hole

Application

For Screw Mount

General

Catalog Number	CT50175MH10C0
Color	Black
EU RoHS Indicator	Yes
Material	NYLON 6/6
Mounting Method	Screw
Operating Temperature Celcius Max	85 °C
Operating Temperature Celcius Min	-40 °C
Rating - Minimum Tensile Strength lbs	50
Sub Brand	UNIRAP,CABLE TIE
Trade Name	UNIRAP™
Type	Standard
UPC	781810335260

Dimensions

Dimension - Bundle Diameter Max inch	1.75 in
Dimension - L Length Overall mm	203 mm
Dimension - Length Overall inch	8.00 in
Dimension - Screw Size inch	#10
Dimension - Width inch	0.17 in
Dimension - Width mm	4 mm

Certifications And Compliance

Certification - 94V0 Rated	N
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - UV Rated	Yes
Certification - cULus	Yes
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	5000
Minimum Pack Quantity	100

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Catalogs - Section G - Wire Management](#)
[Product Cross Section Image\(s\) -
BUR_CT_MH_UNIRAP_CABLE_TIE_LineArt](#)
[Sales Drawings - 50080813](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-CT50175MH10C0-SPEC-EN | REV 6/2024