



# CT50175MH10CUG, Cable Tie, 1.75" Max Bundle, 50 Lb Tensile, Natural, Universal Grade, Screw Mount

By Burndy

Catalog # [CT50175MH10CUG](#)



Natural Nylon 6/6 Universal Grade Cable Tie, Tensile Strength-50Lbs, 7.79"L, 0.18"W, 1.75" Max. Bundle Dia.

## Features

Mounting Hole

## General

Catalog Number	CT50175MH10CUG
Color	Natural
Material	Nylon 6/6
Rating - Minimum Tensile Strength lbs	50
Tool Type	Standard
Trade Name	UNIRAP™
UPC	781810469194

## Dimensions

Dimension - Bundle Diameter Max inch	1.75
Dimension - L Length Overall mm	198 mm
Dimension - Length Overall inch	7.79 in
Dimension - Screw Size inch	#10
Dimension - Width inch	0.18 in
Dimension - Width mm	4.6 mm

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	Yes
Certification - UV Rated	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

## Logistics

Carton Quantity	10000
Minimum Pack Quantity	100

## Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section G - Wire Management](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_CT\\_MH\\_UNIRAP\\_CABLE\\_TIE\\_LineArt](#)
- [Sales Drawings - 10092186](#)
- [Specifications - CT50175MH10CUG](#)