



CT50175SSBC, Nylon Cable Tie, 50 lb Tensile Strength, Stainless Steel Barb, 1.77" Bundle, Natural

By Burndy
Catalog # [CT50175SSBC](#)

Nylon 6/6 Cable Tie with Stainless steel Barb, 50 Lbs, Natural, 1.77" Bundle Dia., Package: 100.



Features

Stainless Steel Barb Tie

Application

For use with self-locking stainless steel barb

General

Catalog Number	CT50175SSBC
Color	Natural
EU RoHS Indicator	Yes
Material	NYLON 6/6
Rating - Minimum Tensile Strength lbs	50
Sub Brand	UNIRAP,CABLE TIE
Trade Name	UNIRAP™
Type	CT_SSB
UPC	781810564615

Dimensions

Dimension - Bundle Diameter Max inch	1.77
Dimension - L Length Overall mm	186 mm
Dimension - Length Overall inch	7.32 in
Dimension - Width inch	0.19 in
Dimension - Width mm	5 mm

Certifications And Compliance

Buy American Compliant	No
Certification - CSA Approved	Yes
Certification - ETL	No
Certification - cULus	Y
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	8000
Minimum Pack Quantity	100

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section G - Wire Management](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 30022708](#)
[Specifications - CT50175SSBC](#)