



# CT50175SSBC0, Nylon Cable Tie, 50 lb Tensile Strength, Stainless Steel Barb, 1.77" Bundle, Black

By Burndy  
Catalog # [CT50175SSBC0](#)

Nylon Stainless Steel BARB Cable Ties, 7.32 IN L, .19 IN W, Tensile Strength: 50 Lbs,max bundle dia:1.77".



## Features

Stainless Steel Barb Tie

## Application

For use with self-locking stainless steel barb

## General

Catalog Number	CT50175SSBC0
Color	Black
EU RoHS Indicator	Yes
Material	NYLON 6/6
Rating - Minimum Tensile Strength lbs	50
Sub Brand	UNIRAP,CABLE TIE
Trade Name	UNIRAP™
Type	CT_SSB
UPC	781810564622

## Dimensions

Dimension - Bundle Diameter Max inch	1.77
Dimension - L Length Overall mm	186 mm

Dimension - Length Overall inch	7.32 in
Dimension - Width inch	0.19 in
Dimension - Width mm	5 mm

## Certifications And Compliance

Buy American Compliant	No
Certification - CSA Approved	Yes
Certification - ETL	No
Certification - cULus	Y
Standards - RoHS Compliance Status	CM

## Logistics

Carton Quantity	8000
Minimum Pack Quantity	100

## Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section G - Wire Management](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 30022708](#)
- [Specifications - CT50175SSBC0](#)