



CT50200SSBC0, Nylon Cable Tie, 50 lb Tensile Strength, Stainless Steel Barb, 7.87" Long, Black

By Burndy

Catalog # [CT50200SSBC0](#)

Nylon Stainless Steel BARB Cable Ties, 7.87 IN L, .24 IN W,
Tensile Strength: 50 Lbs,Color:Black.



Features

Stainless Steel Barb Tie

Application

For use with self-locking stainless steel barb

General

Catalog Number	CT50200SSBC0
Color	Black
EU RoHS Indicator	Yes
Material	NYLON 6/6
Rating - Minimum Tensile Strength lbs	50
Sub Brand	UNIRAP,CABLE TIE
Trade Name	UNIRAP™
Type	CT_SSB
UPC	781810564745

Dimensions

Dimension - Bundle Diameter Max inch	1.97
Dimension - L Length Overall mm	200 mm

Dimension - Length Overall inch	7.87 in
Dimension - Width inch	0.24 in
Dimension - Width mm	6 mm

Certifications And Compliance

Buy American Compliant	No
Certification - CSA Approved	Yes
Certification - ETL	No
Certification - cULus	Y
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	6000
Minimum Pack Quantity	100

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section G - Wire Management](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 30022708](#)
[Specifications - CT50200SSBC0](#)