



CT50250IDC, Cable Tie, 50 Lb Tensile, Natural, Identification

By Burndy
Catalog # [CT50250IDC](#)

Nylon 6/6, Color:Natural, Bundle dia:7.1 MM.



Features

Identification

Application

Identification Cable Ties Are Used In Both Bundling And Identifying Wire Groups At The Same Time

General

Catalog Number	CT50250IDC
EU RoHS Indicator	Contact Manufacturer
Material	NYLON 6/6
Rating - Minimum Tensile Strength lbs	50 Lb
Sub Brand	UNIRAP
Trade Name	UNIRAP™
Type	Cable Ties
UPC	621945443457

Dimensions

Dimension - Bundle Diameter Max inch	2.95 in
Dimension - L Length Overall mm	270 mm

Dimension - Length Overall inch	10.6 in
Dimension - Width inch	0.18 in
Dimension - Width mm	4.6 mm

Certifications And Compliance

Buy American Compliant	Under Review
Certification - CSA Approved	No
Standards - RoHS Compliance	CM
Status	

Logistics

Carton Quantity	7500
Minimum Pack Quantity	100

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section G - Wire Management](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50055369](#)
- [Specifications - CT50250IDC](#)