



CT50300C, Cable Tie, 3" Max Bundle, 50 Lb Tensile, Natural

By Burndy
Catalog # [CT50300C](#)



Natural Nylon 6/6 Cable Tie, 3" Max. Bundle Dia, 50 Lbs, 11.75" Long.

Features

- Standard Cable Tie

Application

For General Purpose

General

| | |
|---------------------------------------|---|
| Color | <ul style="list-style-type: none">• Natural• Naturel |
| Material | NYLON 6/6 |
| Military Specification | MS3367 |
| Operating Temperature Celcius Max | 85 °C |
| Operating Temperature Celcius Min | -40 °C |
| Rating - Minimum Tensile Strength lbs | 50 |
| Sub Brand | UNIRAP,CABLE TIE |
| Tool Type | Standard |
| Trade Name | UNIRAP™ |
| Type | Standard |
| UPC | 781810332566 |

Dimensions

| | |
|--------------------------------------|----------|
| Dimension - Bundle Diameter Max inch | 3 |
| Dimension - L Length Overall mm | 286 mm |
| Dimension - Length Overall inch | 11.25 in |
| Dimension - Width inch | 0.18 in |
| Dimension - Width mm | 5 mm |

Certifications and Compliance

| | |
|------------------------------------|-------------------------------|
| Certification - 94V0 Rated | No |
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - UV Rated | No |
| Certification - cULus | No |
| Industry Standard(s) | Military Specified (Mil-Spec) |
| Military Spec Number | MS3367-7-9 |
| Standards - Industry Standards Met | Military Specified (Mil-Spec) |
| Standards - RoHS Compliance Status | CM |
| UL Listed | No |

Logistics

| | |
|-----------------------|------|
| Carton Quantity | 5000 |
| Minimum Pack Quantity | 100 |

Product Assets

[3D Models - CT50300C_MODEL-PDF](#)
[3D Models - CT50300C_MODEL-STEP](#)
[3D Models - CT50300C_MODEL-IGES](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Sales Drawings - 50080813](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-CT50300C-SPEC-EN | REV 1/2024