



CT50300C00, Cable Tie, 3" Max Bundle, 50 Lb Tensile, UV Black

By Burndy
Catalog # CT50300C00



Nylon cable ties, Tensile strength-50 Lbs, Color- UV Black, 11.25"L, 0.18"W, 03.00" Bundle Dia.

Features

Standard Cable Tie

General

Catalog Number	CT50300C00
Color	UV Black (Mil. Spec.)
Material	NYLON 6/6
Military Specification	MS3367
Operating Temperature Celcius Max	85 °C
Operating Temperature Celcius Min	-40 °C
Rating - Minimum Tensile Strength lbs	50
Tool Type	Standard
Trade Name	UNIRAP™
UPC	781810332825

Dimensions

Dimension - Bundle Diameter Max inch	3
Dimension - L Length Overall mm	286 mm
Dimension - Length Overall inch	11.25 in
Dimension - Width inch	0.18 in
Dimension - Width mm	5 mm

Certifications And Compliance

Certification - 94V0 Rated	N
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - UV Rated	Yes
Certification - cULus	No
Industry Standard(s)	Military Specified (Mil-Spec)
Military Spec Number	MS3367-7-0
Standards - Industry Standards Met	Military Specified (Mil-Spec)
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Carton Quantity	5000
Minimum Pack Quantity	100
Packaging Type	Bag

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section G - Wire Management](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_CT_UNIRAP_CABLE_TIE_LineArt](#)
[Sales Drawings - 50080813](#)
[Specifications - CT50300C00](#)



A Hubbell brand