



CT50300M0, Cable Tie, 1.25" Max Bundle, 30 Lb Tensile, UV Black

By Burndy
Catalog # [CT50300M0](#)



UV Black1 Nylon 6/6 Cable Tie, 3" Max. Bundle Dia, 50 Lbs, 11.75" Long, 0.18" Wide.

Features

Standard Cable Tie

Application

For Outdoor Applications

General

Catalog Number	CT50300M0
Color	Black
EU RoHS Indicator	Yes
Material	NYLON 6/6
Military Specification	MS3367
Operating Temperature Celcius Max	85 °C
Operating Temperature Celcius Min	-40 °C
Rating - Minimum Tensile Strength lbs	50
Sub Brand	UNIRAP,CABLE TIE
Trade Name	UNIRAP™
Type	Standard
UPC	781810332894

Dimensions

Dimension - Bundle Diameter Max inch	3
Dimension - L Length Overall mm	282 mm
Dimension - Length Overall inch	11.1 in

Dimension - Width inch	0.18 in
Dimension - Width mm	5 mm

Certifications And Compliance

Buy American Compliant	Yes
Certification - 94V0 Rated	N
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - UV Rated	Yes
Certification - cULus	No
Industry Standard(s)	Military Specified (Mil-Spec)
Military Spec Number	MS3367-7-0
Standards - Industry Standards Met	Military Specified (Mil-Spec)
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	5000
Minimum Pack Quantity	1000

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_CT_UNIRAP_CABLE_TIE_LineArt](#)
[Sales Drawings - 50080813](#)
[Specifications - CT50300M0](#)