



CT50300MH10COUG, Cable Tie, 50 Lb Tensile, UV Black, Universal Grade, Screw Mount

By Burndy
Catalog # [CT50300MH10COUG](#)



Nylon UNIRAP™ Cable Tie - 50 Lb. Tensile Strength (Universal Grade).

Features

Mounting Hole

General

Catalog Number	CT50300MH10COUG
Color	Black
Grounding Style	
Material	NYLON 6/6
Rating - Minimum Tensile Strength lbs	50
Tool Type	Standard
UPC	781810655566
Volume	30

Dimensions

Depth	2.125
Dimension - Bundle Diameter Max inch	3
Dimension - L Length Overall mm	298 mm
Dimension - Length Overall inch	11.73 in
Dimension - Screw Size inch	#10
Dimension - Width inch	0.18 in
Dimension - Width mm	5 mm

Certifications And Compliance

Certification - CSA Approved	Yes
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	5000
Minimum Pack Quantity	1000
Pallet Quantity	35

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section G - Wire Management](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 10092186](#)
- [Specifications - CT50300MH10COUG](#)