



# CT50300MUG, Cable Tie, 3" Max Bundle, 50 Lb Tensile, Natural, Universal Grade



By Burndy  
Catalog # [CT50300MUG](#)

Nylon cable ties, Tensile strength-50 Lbs, Color- Natural, 11.34"L, 0.18"W, 03.00" Bundle Dia.

## Features

Standard Cable Tie

## General

Catalog Number	CT50300MUG
Color	Natural
Material	NYLON 6/6
Rating - Minimum Tensile Strength N	50
Rating - Minimum Tensile Strength lbs	50 Lb
Tool Type	Standard
Trade Name	UNIRAP™
UPC	781810469095

## Dimensions

Dimension - Bundle Diameter Max inch	3
Dimension - L Length Overall mm	288 mm
Dimension - Length Overall inch	11.34 in
Dimension - Width inch	0.18 in
Dimension - Width mm	4.6 mm

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	Yes
Certification - UV Rated	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

## Logistics

Carton Quantity	5000
Minimum Pack Quantity	1000

## Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section G - Wire Management](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_CT\\_UNIRAP\\_CABLE\\_TIE\\_LineArt](#)
- [Sales Drawings - 10092186](#)
- [Specifications - CT50300MUG](#)