



## CT50300SSBC, Nylon Cable Tie, 50 lb Tensile Strength, Stainless Steel Barb, 11.61" Long, Natural

By Burndy  
Catalog # [CT50300SSBC](#)

Nylon Stainless Steel BARB Cable Ties, 11.61 IN L, .19 IN W, Tensile Strength: 50 Lbs,Color:Natural.



### Features

Stainless Steel Barb Tie

### Application

For use with self-locking stainless steel barb

### General

Catalog Number	CT50300SSBC
Color	Natural
EU RoHS Indicator	Yes
Material	NYLON 6/6
Rating - Minimum Tensile Strength lbs	50
Sub Brand	UNIRAP,CABLE TIE
Trade Name	UNIRAP™
Type	CT_SSB
UPC	781810564660

### Dimensions

Dimension - Bundle Diameter Max inch	3.19
Dimension - L Length Overall mm	295 mm
Dimension - Length Overall inch	11.61 in
Dimension - Width inch	.19 in
Dimension - Width mm	5 mm

### Certifications And Compliance

Buy American Compliant	No
Certification - CSA Approved	Yes
Certification - ETL	No
Certification - cULus	Y
Standards - RoHS Compliance Status	CM

### Logistics

Carton Quantity	6000
Minimum Pack Quantity	100

### Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section G - Wire Management](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 30022708](#)
- [Specifications - CT50300SSBC](#)