



# CT50400MH10CO, Cable Tie, 4" Max Bundle, 50 Lb Tensile, UV Black, Screw Mount

By Burndy  
Catalog # [CT50400MH10CO](#)

Nylon cable ties, Tensile strength-50 Lbs, Color- UV Black,  
14.50"L, 0.17"W, 04.00" Bundle Dia.



## Features

- Mounting Hole

## Application

Bundling and mounting, one easy installation. Ideal for use where bundle needs to be secured, such as control panels and ceilings

## General

Color	Black
Material	NYLON 6/6
Mounting Method	Screw
Operating Temperature Celcius Max	85 °C
Operating Temperature Celcius Min	-40 °C
Rating - Minimum Tensile Strength lbs	50
Sub Brand	UNIRAP
Trade Name	UNIRAP™
Type	CT-MH
UPC	781810335307

## Dimensions

Dimension - Bundle Diameter Max inch	4
Dimension - L Length Overall mm	368 mm
Dimension - Length Overall inch	14.50 in
Dimension - Screw Size inch	#10
Dimension - Width inch	0.18 in
Dimension - Width mm	5 mm
Length	15.25 in

## Certifications and Compliance

Certification - 94V0 Rated	No
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - UV Rated	Yes
Certification - cULus	Yes
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Carton Quantity	1000
Minimum Pack Quantity	1000
Packaging Type	Bag

## Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Sales Drawings - 50080813](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY-CT50400MH10CO-SPEC-EN | REV 1/2024