



**CT50400MH10CO, Cable Tie, 4"
Max Bundle, 50 Lb Tensile, UV
Black, Screw Mount**

By Burndy
Catalog # [CT50400MH10CO](#)

Nylon cable ties, Tensile strength-50 Lbs, Color- UV Black,
14.50"L, 0.17"W, 04.00" Bundle Dia.



Features

Mounting Hole

Application

Bundling and mounting, one easy installation. Ideal for use where bundle needs to be secured, such as control panels and ceilings

General

Color	Black
EU RoHS Indicator	Yes
Material	NYLON 6/6
Mounting Method	Screw
Operating Temperature Celcius Max	85 °C
Operating Temperature Celcius Min	-40 °C
Rating - Minimum Tensile Strength lbs	50
Sub Brand	UNIRAP
Trade Name	UNIRAP™
Type	CT-MH
UPC	781810335307

Dimensions

Dimension - Bundle Diameter Max inch	4
Dimension - L Length Overall mm	368 mm
Dimension - Length Overall inch	14.50 in
Dimension - Screw Size inch	#10
Dimension - Width inch	0.18 in
Dimension - Width mm	5 mm
Length	15.25 in

Certifications And Compliance

Certification - 94V0 Rated	N
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - UV Rated	Yes
Certification - cULus	Yes
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	1000
Minimum Pack Quantity	1000
Packaging Type	Bag

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Product Cross Section Image\(s\) - BUR_CT_MH_UNIRAP_CABLE_TIE_LineArt](#)
[Sales Drawings - 50080813](#)



A proud member of the Hubbell Family.