



CT50400RC0, Cable Tie, 4" Max Bundle, 50 Lb Tensile, UV Black, Releasable

By Burndy
Catalog # [CT50400RC0](#)



Nylon cable ties, Tensile strength-50 Lbs, Color- UV Black, 14.60"L, 0.18"W, 04.00" Bundle Dia.

Features

Releaseable

General

Catalog Number	CT50400RC0
Color	Black
Material	NYLON 6/6
Operating Temperature Celcius Max	85 °C
Operating Temperature Celcius Min	-40 °C
Rating - Minimum Tensile Strength lbs	50
Trade Name	UNIRAP™
UPC	781810334744

Dimensions

Dimension - Bundle Diameter Max inch	4
Dimension - L Length Overall mm	371 mm
Dimension - Length Overall inch	14.60 in
Dimension - Width inch	0.18 in
Dimension - Width mm	4.6 mm

Certifications And Compliance

Certification - CSA Approved	No
Certification - UV Rated	Yes
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	5000
Minimum Pack Quantity	1000
Packaging Type	Bag

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section G - Wire Management](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_CT_UNIRAP_REL_CABLETIE_LineArt](#)
- [Sales Drawings - 50034344](#)
- [Specifications - CT50400RC0](#)