



CT50400SSBB, Nylon Cable Tie, 50 lb Tensile Strength, Stainless Steel Barb, 3.94" Bundle, Natural

By Burndy
Catalog # [CT50400SSBB](#)

Nylon 6/6 Cable Tie with Stainless steel Barb, 50 Lbs, Natural, 3.94" Bundle Dia., Package: 250.

Features

Stainless Steel Barb Tie

Application

For use with self-locking stainless steel barb

General

Catalog Number	CT50400SSBB
Color	Natural
EU RoHS Indicator	Yes
Material	NYLON 6/6
Rating - Minimum Tensile Strength lbs	50 Lb
Sub Brand	CABLE TIE, UNIRAP
Trade Name	UNIRAP™
Type	CT_SSB
UPC	781810565308

Dimensions

Dimension - Bundle Diameter Max inch	3.94 in
Dimension - L Length Overall mm	364 mm



Dimension - Length Overall inch	14.33 in
Dimension - Width inch	0.19 in
Dimension - Width mm	5 mm

Certifications And Compliance

Buy American Compliant	No
Certification - CSA Approved	Yes
Certification - ETL	No
Certification - cULus	Y
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	5000
Minimum Pack Quantity	500

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section G - Wire Management](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 30022708](#)
- [Specifications - CT50400SSBB](#)