



## CTB075AA4C, Cable Tie Mounting Base, Acrylic Adhesive

By Burndy  
Catalog # [CTB075AA4C](#)

Nylon Cable tie mounting bases, Color:Natural, 0.74" L, 0.74" W,  
Max Tie Slot Width: 0.20", Tensile Strength: 11 Lbs.

### Features

Cable Tie Base

### General

Catalog Number	CTB075AA4C
Color	Natural
Material	NYLON 6/6
Mounting Method	Acrylic adhesive or #4 screw
Operating Temperature Celcius Max	70 °C
Operating Temperature Celcius Min	0 °C
Trade Name	UNIRAP™
Type	Cable Tie Bases
UPC	781810335765

### Dimensions

Dimension - B Length inch	0.74 in
Dimension - Width inch	0.74 in

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - UV Rated	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Carton Quantity	1000
Minimum Pack Quantity	100
Packaging Type	Bag

### Product Assets

- [3D Models - CTB075AA4C\\_MODEL-IGES](#)
- [3D Models - CTB075AA4C\\_MODEL-STEP](#)
- [3D Models - CTB075AA4C\\_MODEL-PDF](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_CTB\\_MOUNTING\\_BASE\\_LineArt](#)
- [Sales Drawings - 50080810](#)
- [Specifications - CTB075AA4C](#)