



CTB075AA4C0, Cable Tie Mounting Base, Acrylic Adhesive, Black

By Burndy
Catalog # [CTB075AA4C0](#)

Nylon Cable tie mounting bases, Color:Black, 0.74" L, 0.74" W,
Max Tie Slot Width: 0.20", Tensile Strength: 11 Lbs.



Features

Cable Tie Base

General

Catalog Number	CTB075AA4C0
Color	Black
Material	NYLON 6/6
Mounting Method	Acrylic adhesive or #4 screw
Operating Temperature Celcius Max	70 °C
Operating Temperature Celcius Min	0 °C
Trade Name	UNIRAP™
Type	Cable Tie Bases
UPC	781810335772

Dimensions

Dimension - B Length inch	0.74 in
Dimension - Width inch	0.74 in

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - UV Rated	Yes
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Carton Quantity	1000
Minimum Pack Quantity	1000
Packaging Type	Bag

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_CTB_MOUNTING_BASE_LineArt](#)
- [Sales Drawings - 50080810](#)
- [Specifications - CTB075AA4C0](#)