



## CTB075AA4M, Cable Tie Mounting Base, Acrylic Adhesive, Natural

By Burndy

Catalog # [CTB075AA4M](#)

Nylon Cable tie mounting bases, Color:Natural, 0.75" L, 0.75" W, Max Tie Slot Width: 0.14".

### Features

Cable Tie Base

### General

Catalog Number	CTB075AA4M
Color	Natural
Material	NYLON 6/6
Mounting Method	Acrylic adhesive or #6 or #8 Screw
Operating Temperature Celcius Max	70 °C
Operating Temperature Celcius Min	0 °C
Type	Cable Tie Bases
UPC	781810335789

### Dimensions

Dimension - B Length inch	0.75 in
Dimension - Width inch	0.75 in

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - UV Rated	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

### Logistics

Minimum Pack Quantity	10000
Packaging Type	Bag

### Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_CTB\\_MOUNTING\\_BASE\\_2WAY\\_LineArt](#)
- [Sales Drawings - 50042700](#)
- [Specifications - CTB075AA4M](#)



A Hubbell brand