



## CTB075RA4C, Cable Tie Mounting Base, Rubber Adhesive, Natural

By Burndy  
Catalog # [CTB075RA4C](#)

Rubber Adhesive Cable Tie Mounting Base, 0.14" Max. Tie Slot Width.



### Features

Cable Tie Base

### Application

For used in conjunction with cable ties to stabilize and secure wire bundles

### General

Color	Natural
EU RoHS Indicator	Yes
Material	NYLON 6/6
Mounting Method	Rubber adhesive or #4 screw
Operating Temperature Celcius Max	70 °C
Operating Temperature Celcius Min	0 °C
Sub Brand	UNIRAP,CABLE TIE
Trade Name	UNIRAP™
Type	Cable Tie Bases
UPC	781810335802

### Dimensions

Dimension - B Length inch	0.74 in
Dimension - Width inch	0.74 in

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - UV Rated	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Carton Quantity	1000
Minimum Pack Quantity	100

### Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Product Cross Section Image\(s\) - BUR\\_CTB\\_MOUNTING\\_BASE\\_LineArt](#)  
[Sales Drawings - 50080810](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY-CTB075RA4C-SPEC-EN | REV 5/2024