



## CTB075RA4CO, Cable Tie Mounting Base, Rubber Adhesive, Black

By Burndy  
Catalog # [CTB075RA4CO](#)

Nylon Cable tie mounting bases, Color:Black, 0.74" L, 0.74" W,  
Max Tie Slot Width: 0.20", Tensile Strength: 9 Lbs.

### Features

Cable Tie Base

### General

Catalog Number	CTB075RA4CO
Color	Black
Material	NYLON 6/6
Mounting Method	Rubber adhesive or #4 screw
Operating Temperature Celcius Max	70 °C
Operating Temperature Celcius Min	0 °C
Trade Name	UNIRAP™
Type	Cable Tie Bases
UPC	781810335819

### Dimensions

Dimension - B Length inch	0.74 in
Dimension - Width inch	0.74 in

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	Yes
Certification - UV Rated	Yes
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Carton Quantity	1000
Minimum Pack Quantity	1000
Packaging Type	Bag

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Product Cross Section Image\(s\) - BUR\\_CTB\\_MOUNTING\\_BASE\\_LineArt](#)  
[Sales Drawings - 50080810](#)  
[Specifications - CTB075RA4CO](#)