



## CTB075RA4M, Cable Tie Mounting Base, Rubber Adhesive, Natural

By Burndy  
Catalog # [CTB075RA4M](#)

Nylon Cable tie mounting bases, Color:Natural, 0.75" L, 0.75" W, Max Tie Slot Width: 0.20", Tensile Strength: 9 Lbs.



### Features

Cable Tie Base

### General

Color	Natural
Material	NYLON 6/6
Mounting Method	Rubber adhesive or #4 screw
Operating Temperature Celcius Max	70 °C
Operating Temperature Celcius Min	0 °C
Trade Name	UNIRAP™
Type	Cable Tie Bases
UPC	781810335826

### Dimensions

Dimension - B Length inch	0.74 in
Dimension - Width inch	0.74 in

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	Yes
Certification - UV Rated	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Carton Quantity	1000
Minimum Pack Quantity	1000
Packaging Type	Bag

### Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Product Cross Section Image\(s\) - BUR\\_CTB\\_MOUNTING\\_BASE\\_LineArt](#)  
[Sales Drawings - 50080810](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY-CTB075RA4M-SPEC-EN | REV 5/2024