



CTB100AA4D, Cable Tie Mounting Base, Acrylic Adhesive, Natural

By Burndy
Catalog # [CTB100AA4D](#)

Nylon Cable tie mounting bases, Color:Natural, 1" L, 1" W, Max Tie Slot Width: 0.20", Tensile Strength: 30 Lbs.



Features

Cable Tie Base

General

Color	Natural
Material	NYLON 6/6
Mounting Method	Rubber adhesive or #10 screw
Operating Temperature Celcius Max	70 °C
Operating Temperature Celcius Min	0 °C
Type	Cable Tie Bases
UPC	781810663110

Dimensions

Dimension - B Length inch	1 in
Dimension - Width inch	1 in

Certifications And Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

Logistics

Minimum Pack Quantity	500
Packaging Type	Bag

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Sales Drawings - 50042700](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-CTB100AA4D-SPEC-EN | REV 6/2024