



CTB150RA4C, Cable Tie Mounting Base, Rubber Adhesive, Natural

By Burndy
Catalog # [CTB150RA4C](#)

Nylon Cable tie mounting bases, Color:Natural, 1.51" L, 1.51" W, Max Tie Slot Width: 0.39".

Features

Cable Tie Base

General

Catalog Number	CTB150RA4C
Color	Natural
Material	NYLON 6/6
Mounting Method	Rubber adhesive or #10 screw
Operating Temperature Celcius Max	70 °C
Operating Temperature Celcius Min	0 °C
Trade Name	UNIRAP™
Type	Cable Tie Bases
UPC	781810336007

Dimensions

Dimension - B Length inch	1.51 in
Dimension - Width inch	1.51 in

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - UV Rated	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Carton Quantity	2500
Minimum Pack Quantity	100
Packaging Type	Bag

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section G - Wire Management](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_CTБ_MOUNTING_BASE_LineArt](#)
- [Sales Drawings - 50101822](#)
- [Specifications - CTB150RA4C](#)