




CTHS50700MCTHS50700M, Heat Stabilized Nylon Cable Tie, 50 Lb Tensile Strength, 1.87" Bundle, Black

By Burndy
Catalog # CTHS50700M



Heat Stabilized Nylon 6/6 cable ties, Color: UV Black, Tensile Strength: 50 Lb, 7.56" L, 0.18"W, 1.87" Bundle Dia.

Features

Heat Stabilized Cable Tie

General

Catalog Number	CTHS50700M
Color Code	Black
Material	NYLON 6/6
Operating Temperature Celcius Max	105 °C
Operating Temperature Celcius Min	-40 °C
Rating - Minimum Tensile Strength lbs	50
UPC	781810661048
UPC 12 Digit	7818106610488

Dimensions

Dimension - Bundle Diameter Max inch	1.88
Dimension - L Length Overall mm	192 mm
Dimension - Length Overall inch	7.56 in
Dimension - Width inch	0.18 in
Dimension - Width mm	5 mm

Certifications And Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Logistics

Carton Quantity	1000
Minimum Pack Quantity	1
Packaging Type	Bag

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section G - Wire Management](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50080813](#)
- [Specifications - CTHS50700M](#)