



CTNT50275C0, Cable Tie, 2.75" Max Bundle, 50 Lb Tensile, Black, Nylon 12

By Burndy
Catalog # [CTNT50275C0](#)

Nylon 12 Cable Tie, Tensile strength: 50 Lbs, Color: Black,
11.00"L, 0.19"W, 2.75" Bundle Dia.



Application

Indoor and Outdoor mounting applications

General

| | |
|---------------------------------------|--------------|
| Color | Black |
| Construction Material - Main | Nylon |
| Material | NYLON 12 |
| Rating - Minimum Tensile Strength lbs | 50 lb |
| Sub Brand | UNIRAP |
| Tensile Strength | 50 lb. |
| Trade Name | UNIRAP™ |
| Type | Cable Tie |
| UPC | 621945469433 |

Dimensions

| | |
|--------------------------------------|----------|
| Dimension - Bundle Diameter Max inch | 2.75 in |
| Dimension - L Length Overall mm | 280 mm |
| Dimension - Length Overall inch | 11.00 in |
| Dimension - Width inch | 0.19 in |
| Dimension - Width mm | 4.8 mm |
| Thickness | 0.06 in |

Certifications and Compliance

Certification - CSA Approved No
Standards - RoHS Compliance CM
Status

Logistics

Carton Quantity 1000
Minimum Pack Quantity 100

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Sales Drawings - 50071686](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-CTNT50275C0-SPEC-EN | REV 1/2024