



# CTNT50275D0, Cable Tie, 2.75" Max Bundle, 50 Lb Tensile, Black, Nylon 12

By Burndy  
Catalog # [CTNT50275D0](#)

Nylon 12 Cable Tie, Tensile strength: 50 Lbs, Color: Black, 11.00"L,  
0.19"W, 2.75" Bundle Dia.

## Features

- Nylon 12 Cable Ties provide excellent UV, chemical and moisture resistant
- Ties feature inside serrations and bent tail for quick, easy installation
- Smooth edge to prevent bundle damage
- Especially suitable in high moisture, corrosive (zinc chloride and dilute acids) environments
- Good in low temperatures
- Indoor/Outdoor applications

## General

Catalog Number	CTNT50275D0
Color	Black
Material	NYLON 12
Rating - Minimum Tensile Strength lbs	50 lb
Tensile Strength	50 / 22 lb./Kg
Trade Name	UNIRAP™
UPC	621945469440

## Dimensions

Dimension - Bundle Diameter	2.75 in
Max inch	



Dimension - L Length Overall	280 mm
mm	
Dimension - Length Overall	11.00 in
inch	
Dimension - Width inch	0.19 in
Dimension - Width mm	4.8 mm
Thickness	0.06 in

## Certifications And Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance	CM
Status	

## Logistics

Carton Quantity	10000
Minimum Pack Quantity	100

## Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section G - Wire Management](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50071686](#)
- [Specifications - CTNT50275D0](#)