



CTNT50650D0, Cable Tie, 6.7" Max Bundle, 50 Lb Tensile, Black, Nylon 12

By Burndy
Catalog # [CTNT50650D0](#)



Nylon 12 Cable Tie, Tensile strength: 50 Lbs, Color: Black,
23.62"L, 0.19"W, 6.70" Bundle Dia.

General

Color	Black
Material	NYLON 12
Rating - Minimum Tensile Strength lbs	50 lb
Tensile Strength	50 / 22 lb./Kg
Trade Name	UNIRAP™
UPC	621945469389

Dimensions

Dimension - Bundle Diameter Max inch	6.70 in
Dimension - L Length Overall mm	600 mm
Dimension - Length Overall inch	23.62 in
Dimension - Width inch	0.19 in
Dimension - Width mm	4.8 mm
Thickness	0.063 in

Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	5000
Minimum Pack Quantity	500

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Sales Drawings - 50071686](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-CTNT50650D0-SPEC-EN | REV 1/2024