



CTSS100300FC304C, 304 Stainless Steel Cable Tie, 160 lb Tensile, Fully Coated, 3" Bundle

By Burndy

Catalog # [CTSS100300FC304C](#)

Fully coated stainless steel cable ties 304 grade, Tensile strength: 160 Lb, 11.81" L, 0.18" W, 3.00" Bundle Dia.

Features

Stainless Steel Cable Tie - Fully Coated

General

Catalog Number	CTSS100300FC304C
Connector Type	FULLY COATED
Material	304 STAINLESS STEEL
Operating Temperature Celcius Max	115 °C
Operating Temperature Celcius Min	-40 °C
Operating Temperature Range Celcius	-40 - 115
Rating - Minimum Tensile Strength lbs	160
Trade Name	UNIRAP™
UPC	781810646984

Dimensions

Dimension - Bundle Diameter Max inch	3
Dimension - L Length Overall mm	300 mm
Dimension - Length Overall inch	11.81 in



Dimension - Width inch	0.18 in
Dimension - Width mm	4.6 mm

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	5000
Minimum Pack Quantity	100

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section G - Wire Management](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_CTSSFCPC_Lineart](#)
- [Sales Drawings - 50020256](#)
- [Specifications - CTSS100300FC304C](#)