



# CTSS225500304C, 304 Stainless Steel Cable Tie, 225 lb Tensile, 5.04" Bundle

By Burndy

Catalog # [CTSS225500304C](#)

Uncoated stainless steel cable ties 304 grade, Tensile strength: 225 Lb, 19.68" L, 0.18" W, 5.04" Bundle Dia.



## Features

- Smooth, rounded edges help ensure safe, efficient handling
- Ergonomically designed installation tools consistently tensions and cuts off ties leaving flush edges
- Flame retardant and non-toxic for applications where safety from fire is critical

## General

Catalog Number	CTSS225500304C
Connector Type	UNCOATED
Material	304 STAINLESS STEEL
Operating Temperature Celcius Max	300 °C
Operating Temperature Celcius Min	-40 °C
Operating Temperature Range Celcius	-40 - 300
Operating Temperature Range Fahrenheit	-
Rating - Minimum Tensile Strength lbs	225
Trade Name	UNIRAP™
UPC	781810651407

## Dimensions

Dimension - Bundle Diameter Max inch	5.04
--------------------------------------	------

Dimension - L Length Overall mm 500 mm

Dimension - Length Overall inch 19.68 in

Dimension - Width inch 0.18 in

Dimension - Width mm 4.6 mm

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Carton Quantity	3000
Minimum Pack Quantity	100

## Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section G - Wire Management](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_CTSS\\_Lineart](#)
- [Sales Drawings - 50025551](#)
- [Specifications - CTSS225500304C](#)