



# CTSS225600304C, 304 Stainless Steel Cable Tie, 225 lb Tensile, 6.07" Bundle

By Burndy  
Catalog # [CTSS225600304C](#)



Uncoated stainless steel cable ties 304 grade, Tensile strength: 225 Lb, 23.62" L, 0.18" W, 6.07" Bundle Dia.

### Features

- Smooth, rounded edges help ensure safe, efficient handling
- Ergonomically designed installation tools consistently tensions and cuts off ties leaving flush edges
- Flame retardant and non-toxic for applications where safety from fire is critical

### General

Catalog Number	CTSS225600304C
Connector Type	UNCOATED
Material	304 STAINLESS STEEL
Operating Temperature Celcius Max	300 °C
Operating Temperature Celcius Min	-40 °C
Operating Temperature Range Celcius	-40 - 300
Operating Temperature Range Fahrenheit	-
Rating - Minimum Tensile Strength lbs	225
Trade Name	UNIRAP™
UPC	781810651414

### Dimensions

Dimension - Bundle Diameter Max inch	6.07
--------------------------------------	------

Dimension - L Length Overall mm	600 mm
Dimension - Length Overall inch	23.62 in
Dimension - Width inch	0.18 in
Dimension - Width mm	4.6 mm

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Carton Quantity	2500
Minimum Pack Quantity	100

### Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section G - Wire Management](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_CTSS\\_Lineart](#)
- [Sales Drawings - 50025551](#)
- [Specifications - CTSS225600304C](#)