



CTSS2501000Q, 304 Stainless Steel Cable Tie, 250 lb Tensile

By Burndy
Catalog # [CTSS2501000Q](#)



UNIRAP Cable Ties Stainless Steel.

Features

- Smooth, rounded edges help ensure safe, efficient handling
- Ergonomically designed installation tools consistently tensions and cuts off ties leaving flush edges
- Flame retardant and non-toxic for applications where safety from fire is critical

General

Color	Natural
Material	Stainless Steel
Rating - Minimum Tensile Strength N	250
Trade Name	UNIRAP™
UPC	781810368220
UPC 12 Digit	7818103682200

Dimensions

Dimension - Bundle Diameter Max inch	10
Dimension - L Length Overall mm	838 mm
Dimension - Length Overall inch	33 in
Dimension - Pad Width inch	0.39 in

Certifications And Compliance

Certification - CSA Approved	No
Certification - UV Rated	No
Standards - RoHS Compliance Status	UI

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)



A proud member of the Hubbell Family.