



# CTSS250200FC304L, 304 Stainless Steel Cable Tie, 250 lb Tensile, 7.87" Long, Fully Coated

By Burndy  
Catalog # [CTSS250200FC304L](#)

Fully coated stainless steel cable ties 304 grade, Tensile strength: 250 Lb, 7.87" L, 0.31" W, 1.97" Bundle Dia.



## Features

Stainless Steel Cable Tie - Fully Coated

### General

Connector Type	FULLY COATED
Material	304 STAINLESS STEEL
Operating Temperature Celcius Max	115 °C
Operating Temperature Celcius Min	-40 °C
Operating Temperature Range Celcius	-40 - 115
Rating - Minimum Tensile Strength lbs	250
Trade Name	UNIRAP™
UPC	781810647011

### Dimensions

Dimension - Bundle Diameter Max inch	1.97
Dimension - L Length Overall mm	200 mm
Dimension - Length Overall inch	7.87 in
Dimension - Width inch	0.31 in
Dimension - Width mm	7.9 mm

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Carton Quantity	3500
Minimum Pack Quantity	100

## Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Product Cross Section Image\(s\) - BUR\\_CTSSFCPC\\_Lineart](#)  
[Sales Drawings - 50020256](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY-CTSS250200FC304L-SPEC-EN | REV 5/2024