



# CTSS250400FC304L, 304 Stainless Steel Cable Tie, 250 Lb Tensile, 15.75" Long, Fully Coated

By Burndy  
Catalog # [CTSS250400FC304L](#)

Fully coated stainless steel cable ties 304 grade, Tensile strength: 250 Lb, 15.75" L, 0.31" W, 4.02" Bundle Dia.



## Features

Stainless Steel Cable Tie - Fully Coated

## General

Catalog Number	CTSS250400FC304L
Connector Type	FULLY COATED
Material	304 STAINLESS STEEL
Operating Temperature Celcius Max	115 °C
Operating Temperature Celcius Min	-40 °C
Operating Temperature Range Celcius	-40 - 115
Rating - Minimum Tensile Strength lbs	250
Trade Name	UNIRAP™
UPC	781810647035

## Dimensions

Dimension - Bundle Diameter Max inch	4.02
Dimension - L Length Overall mm	400 mm
Dimension - Length Overall inch	15.75 in
Dimension - Width inch	0.31 in
Dimension - Width mm	7.9 mm

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

## Logistics

Carton Quantity	2000
Minimum Pack Quantity	100

## Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section G - Wire Management](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_CTSSFCPC\\_Lineart](#)
- [Sales Drawings - 50020256](#)
- [Specifications - CTSS250400FC304L](#)