



CTSS250400FC304L, 304 Stainless Steel Cable Tie, 250 Lb Tensile, 15.75" Long, Fully Coated

By Burndy
Catalog # CTSS250400FC304L

Fully coated stainless steel cable ties 304 grade, Tensile strength: 250 Lb, 15.75" L, 0.31" W, 4.02" Bundle Dia.

Features

Stainless Steel Cable Tie - Fully Coated

General

Catalog Number	CTSS250400FC304L
Connector Type	FULLY COATED
Material	304 STAINLESS STEEL
Operating Temperature Celcius Max	115 °C
Operating Temperature Celcius Min	-40 °C
Operating Temperature Range Celcius	-40 - 115
Rating - Minimum Tensile Strength lbs	250
Trade Name	UNIRAP™
UPC	781810647035

Dimensions

Dimension - Bundle Diameter Max inch	4.02
Dimension - L Length Overall mm	400 mm
Dimension - Length Overall inch	15.75 in

Dimension - Width inch	0.31 in
Dimension - Width mm	7.9 mm

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Carton Quantity	2000
Minimum Pack Quantity	100

Product Assets

- Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog
- Catalogs - BURNDY Master Catalog - Section G - Wire Management
- Interactive Catalog - BURNDY Full-Line Digital Catalog
- Product Cross Section Image(s) - BUR_CTSSFCPC_Lineart
- Sales Drawings - 50020256
- Specifications - CTSS250400FC304L