



CTSS250500FC304L, 304 Stainless Steel Cable Tie, 250 Lb Tensile, 19.68" Long, Fully Coated

By Burndy

Catalog # [CTSS250500FC304L](#)

Fully coated stainless steel cable ties 304 grade, Tensile strength: 250 Lb, 19.68" L, 0.31" W, 5.04" Bundle Dia.



Features

Stainless Steel Cable Tie - Fully Coated

General

| | |
|---------------------------------------|---------------------|
| Catalog Number | CTSS250500FC304L |
| Connector Type | FULLY COATED |
| Material | 304 STAINLESS STEEL |
| Operating Temperature Celcius Max | 115 °C |
| Operating Temperature Celcius Min | -40 °C |
| Operating Temperature Range Celcius | -40 - 115 |
| Rating - Minimum Tensile Strength lbs | 250 |
| Trade Name | UNIRAP™ |
| UPC | 781810647042 |

Dimensions

| | |
|--------------------------------------|----------|
| Dimension - Bundle Diameter Max inch | 5.04 |
| Dimension - L Length Overall mm | 500 mm |
| Dimension - Length Overall inch | 19.68 in |

| | |
|------------------------|---------|
| Dimension - Width inch | 0.31 in |
| Dimension - Width mm | 7.9 mm |

Certifications And Compliance

| | |
|------------------------------------|----|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Standards - RoHS Compliance Status | CM |
| UL Listed | No |

Logistics

| | |
|-----------------------|------|
| Carton Quantity | 1500 |
| Minimum Pack Quantity | 100 |

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section G - Wire Management](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_CTSSFCPC_Lineart](#)
- [Sales Drawings - 50020256](#)
- [Specifications - CTSS250500FC304L](#)