



CTSS250600PC304L, 304 Stainless Steel Cable Tie, 250 Lb Tensile, 23.62" Long, Partially Coated

By Burndy

Catalog # [CTSS250600PC304L](#)

Semi coated stainless steel cable ties 304 grade, Tensile strength: 270 Lb, 23.62" L, 0.31" W, 6.06" Bundle Dia.

Features

Stainless Steel Cable Tie - Partially Coated

General

Catalog Number	CTSS250600PC304L
Connector Type	PARTIALLY COATED
Material	304 STAINLESS STEEL
Operating Temperature Celcius Max	115 °C
Operating Temperature Celcius Min	-40 °C
Operating Temperature Range Celcius	-40 - 115
Rating - Minimum Tensile Strength lbs	270
Trade Name	UNIRAP™
UPC	781810647547

Dimensions

Dimension - Bundle Diameter Max inch	6.06
Dimension - L Length Overall mm	600 mm
Dimension - Length Overall inch	23.62 in



Dimension - Width inch	0.31 in
Dimension - Width mm	7.9 mm

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	1500
Minimum Pack Quantity	50

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section G - Wire Management](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_CTSSFCPC_Lineart](#)
- [Sales Drawings - 50020256](#)
- [Specifications - CTSS250600PC304L](#)