



CTSS450500FC304L, 304 Stainless Steel Cable Tie, 450 Lb Tensile, 19.68" Long, Fully Coated

By Burndy
Catalog # [CTSS450500FC304L](#)

Fully coated stainless steel cable ties 304 grade, Tensile strength: 450 Lb, 19.68" L, 0.50" W, 5.04" Bundle Dia.



Features

Stainless Steel Cable Tie - Fully Coated

General

Catalog Number	CTSS450500FC304L
Connector Type	FULLY COATED
Material	304 STAINLESS STEEL
Operating Temperature Celcius	115 °C
Max	
Operating Temperature Celcius	-40 °C
Min	
Operating Temperature Range	-40 - 115
Celcius	
Rating - Minimum Tensile	450
Strength lbs	
Trade Name	UNIRAP™
UPC	781810647127

Dimensions

Dimension - Bundle Diameter	5.04
Max inch	
Dimension - L Length Overall	500 mm
mm	
Dimension - Length Overall	19.68 in
inch	
Dimension - Width inch	0.50 in
Dimension - Width mm	12.7 mm

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Carton Quantity	500
Minimum Pack Quantity	100

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section G - Wire Management](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_CTSSFCPC_Lineart](#)
- [Sales Drawings - 50020256](#)
- [Specifications - CTSS450500FC304L](#)