



# CTSS675200PC304Q, 304 Stainless Steel Cable Tie, 675 Lb Tensile, 7.87" Long, Partially Coated

By Burndy  
Catalog # [CTSS675200PC304Q](#)

Semi coated stainless steel cable ties 304 grade, Tensile strength: 675 Lb, 7.87" L, 0.62" W, 1.97" Bundle Dia.

## Features

Stainless Steel Cable Tie - Partially Coated

## General

Catalog Number	CTSS675200PC304Q
Connector Type	PARTIALLY COATED
Material	304 STAINLESS STEEL
Operating Temperature Celcius Max	115 °C
Operating Temperature Celcius Min	-40 °C
Operating Temperature Range Celcius	-40 - 115
Rating - Minimum Tensile Strength lbs	675
Trade Name	UNIRAP™
UPC	781810647646

## Dimensions

Dimension - Bundle Diameter Max inch	1.97
Dimension - L Length Overall mm	200 mm
Dimension - Length Overall inch	7.87 in



Dimension - Width inch	0.62 in
Dimension - Width mm	15.9 mm

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Carton Quantity	1000
Minimum Pack Quantity	25

## Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section G - Wire Management](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_CTSSFCPC\\_Lineart](#)
- [Sales Drawings - 50020256](#)
- [Specifications - CTSS675200PC304Q](#)