



# CTSS675500FC304Q, 304 Stainless Steel Cable Tie, 675 Lb Tensile, 19.68" Long, Fully Coated

By Burndy

Catalog # [CTSS675500FC304Q](#)

Fully coated stainless steel cable ties 304 grade, Tensile strength: 675 Lb, 19.68" L, 0.62" W, 5.04" Bundle Dia.



## Features

Stainless Steel Cable Tie - Fully Coated

## General

Catalog Number	CTSS675500FC304Q
Connector Type	FULLY COATED
Material	304 STAINLESS STEEL
Operating Temperature Celcius Max	115 °C
Operating Temperature Celcius Min	-40 °C
Operating Temperature Range Celcius	-40 - 115
Rating - Minimum Tensile Strength lbs	675
Trade Name	UNIRAP™
UPC	781810647196

## Dimensions

Dimension - Bundle Diameter Max inch	5.04
Dimension - L Length Overall mm	500 mm
Dimension - Length Overall inch	19.68 in

Dimension - Width inch	0.62 in
Dimension - Width mm	15.9 mm

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Carton Quantity	600
Minimum Pack Quantity	25

## Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section G - Wire Management](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_CTSSFCPC\\_Lineart](#)
- [Sales Drawings - 50020256](#)
- [Specifications - CTSS675500FC304Q](#)

