



CTSS675600PC304Q, 304 Stainless Steel Cable Tie, 675 Lb Tensile, 23.62" Long, Partially Coated

By Burndy
Catalog # [CTSS675600PC304Q](#)



Semi coated stainless steel cable ties 304 grade, Tensile strength: 675 Lb, 23.62" L, 0.62" W, 6.06" Bundle Dia.

Features

Stainless Steel Cable Tie - Partially Coated

General

Connector Type	PARTIALLY COATED
Material	304 STAINLESS STEEL
Operating Temperature Celcius Max	115 °C
Operating Temperature Celcius Min	-40 °C
Operating Temperature Range Celcius	-40 - 115
Rating - Minimum Tensile Strength lbs	675
Trade Name	UNIRAP™
UPC	781810647684

Dimensions

Dimension - Bundle Diameter Max inch	6.06
Dimension - L Length Overall mm	600 mm
Dimension - Length Overall inch	23.62 in
Dimension - Width inch	0.62 in
Dimension - Width mm	15.9 mm

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	500
Minimum Pack Quantity	25

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Product Cross Section Image\(s\) - BUR_CTSSFCPC_Lineart](#)
[Sales Drawings - 50020256](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-CTSS675600PC304Q-SPEC-EN | REV 5/2024