



CTSS900200304L, 304 Stainless Steel Cable Tie, 900 Lb Tensile, 7.87" Long

By Burndy

Catalog # [CTSS900200304L](#)

Uncoated stainless steel cable ties 304 grade, Tensile strength: 920 Lb, 7.87" L, 0.62" W, 1.97" Bundle Dia.



Features

- Smooth, rounded edges help ensure safe, efficient handling
- Ergonomically designed installation tools consistently tensions and cuts off ties leaving flush edges
- Flame retardant and non-toxic for applications where safety from fire is critical

General

Catalog Number	CTSS900200304L
Connector Type	UNCOATED
Material	304 STAINLESS STEEL
Operating Temperature Celcius Max	300 °C
Operating Temperature Celcius Min	-40 °C
Operating Temperature Range Celcius	-40 - 300
Rating - Minimum Tensile Strength lbs	920
Trade Name	UNIRAP™
UPC	781810651575
UPC 12 Digit	7818106515755

Dimensions

Dimension - Bundle Diameter Max inch	1.97
Dimension - L Length Overall mm	200 mm

Dimension - Length Overall inch	7.87 in
Dimension - Width inch	0.62 in
Dimension - Width mm	15.9 mm

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	1300
Minimum Pack Quantity	50

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section G - Wire Management](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_CTSS_Lineart](#)
- [Sales Drawings - 50025551](#)
- [Specifications - CTSS900200304L](#)