



CTSS900400304L, 304 Stainless Steel Cable Tie, 900 Lb Tensile, 15.75" Long

By Burndy

Catalog # [CTSS900400304L](#)

Uncoated stainless steel cable ties 304 grade, Tensile strength: 920 Lb, 15.75" L, 0.62" W, 4.02" Bundle Dia.



Features

- Smooth, rounded edges help ensure safe, efficient handling
- Ergonomically designed installation tools consistently tensions and cuts off ties leaving flush edges
- Flame retardant and non-toxic for applications where safety from fire is critical

General

| | |
|---------------------------------------|---------------------|
| Catalog Number | CTSS900400304L |
| Connector Type | UNCOATED |
| Material | 304 STAINLESS STEEL |
| Operating Temperature Celcius Max | 300 °C |
| Operating Temperature Celcius Min | -40 °C |
| Operating Temperature Range Celcius | -40 - 300 |
| Rating - Minimum Tensile Strength lbs | 920 |
| Trade Name | UNIRAP™ |
| UPC | 781810651599 |

Dimensions

| | |
|--------------------------------------|--------|
| Dimension - Bundle Diameter Max inch | 4.02 |
| Dimension - L Length Overall mm | 400 mm |

| | |
|---------------------------------|---------|
| Dimension - Length Overall inch | 15.75 |
| Dimension - Width inch | 0.62 in |
| Dimension - Width mm | 15.9 mm |

Certifications And Compliance

| | |
|------------------------------------|----|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Standards - RoHS Compliance Status | CM |
| UL Listed | No |

Logistics

| | |
|-----------------------|-----|
| Carton Quantity | 600 |
| Minimum Pack Quantity | 50 |

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section G - Wire Management](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_CTSS_Lineart](#)
- [Sales Drawings - 50025551](#)
- [Specifications - CTSS900400304L](#)