



# CUW26RECG5, Deadend Clamp, #6-2/0 ACSR ASC

By Burndy  
Catalog # [CUW26RECG5](#)



Accom: #6 - 2/0 ACSR #6 - 2/0 ASC.

## General

Catalog Number	CUW26RECG5
Connector Type	Deadend
Material	Aluminum Alloy
Material - Hardware	Galvanized Steel
Plated	Y
Plating Type	Tin - Electro Plated
UPC	621945007857

Conductor - ACSR Str Size Range	(6/1) Raven AWG;2/0 (6/1) Quail AWG 6 (6/1) Turkey AWG-2/0 (6/1) Quail AWG
Conductor - AL Str Size	6 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG;2/0 AWG
Conductor - AL Str Size Range	6 AWG-2/0 AWG

## Dimensions

Dimension - Height fraction	3-22/25 in
Dimension - Height inch	3.88 in
Dimension - Height mm	98.6 mm
Dimension - L Length Overall mm	213 mm
Dimension - Length Overall inch	8.38 in
Dimension - Width fraction	3-15/79 in
Dimension - Width inch	3.19 in
Dimension - Width mm	81 mm

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Minimum Pack Quantity	1
-----------------------	---

## Conductor Related

Conductor - ACSR Str Size	6 (6/1) Turkey AWG;5 (6/1) Thrush AWG;4 (6/1) Swan AWG;4 (7/1) Swanate AWG;3 (6/1) Swallow AWG;2 (6/1) Sparrow AWG;2 (7/1) Sparate AWG;1 (6/1) Robin AWG;1/0
---------------------------	--

## Product Assets

- [3D Models - CUW26RECG5\\_MODEL-PDF](#)
- [3D Models - CUW26RECG5\\_MODEL-IGES](#)
- [3D Models - CUW26RECG5\\_MODEL-STEP](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Literature - Ropes Course Industry Letter \(April 2021\)](#)
- [Sales Drawings - CSC31914](#)
- [Specifications - CUW26RECG5](#)