



CY2/OL20G2 Rope Lay Braid

By Burndy

Catalog # [CY2/OL20G2](#)

Rope Lay Braid.



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

General

Catalog Number	CY2/OL20G2
Connector Type	Braid
Material	Copper
UPC	621945447424
UPC 12 Digit	6219454474244

Dimensions

Dimension - L Length Overall	508
mm	
Dimension - Length Overall	20
inch	
Length	20 in
Weight	1.329 lb

Certifications And Compliance

Certification - CSA Approved	No
------------------------------	----

Logistics

Carton Quantity	10
Minimum Pack Quantity	10
Pallet Quantity	720

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50056945](#)
- [Specifications - CY2/OL20G2](#)
- [Specifications - BURNDY_CY2OL20G2_Specsheet](#)